

WARNING

Analog output lines must not be connected to any kind of voltage or current source, serious damage will result.

Notes

- 1. Power Cord Provided w/ wall plug adapter.
- Audible alarm (Optional) factory wired. Remote Audible and Visual Alarms must be 120VAC and connected to Alarm terminal Strip.
- 3. Sensor Cable between Oxyguard[?] Controller and sensor Maximum Length 200FT. Use 3 conductor 18 or 20ga. w/ foil shield.
- 4. Analog Outputs (Optional) are either 0 5VDC, 0 10VDC, or 4 20mA.